UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 24-6N24

EVAPCO, INC. evapco





DWG. # REV. WB3242412-DRD-ST DATE<sub>11/21/2025</sub> SERIAL #


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]

## **FACE C**







**SHIPPING** 107060 lbs+ [48565] kg+ WEIGHT

**OPERATING** WEIGHT

151320 lbs+ [68640] kg+

HEAVIEST SECTION WEIGHT

23970 lbs+ [10875] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: