UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 9-3K11-Z

EVAPCO, INC. Evapco




DWG. # REV. WB3091106-DRC-SF DATE<sub>11/22/2025</sub> SERIAL #

## NOTES:


- 1. (M) FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS:


**ENGLISH FT-IN** METRIC [mm]





## **FACE A**





**SHIPPING** 11120 lbs+ [5045] kg+ WEIGHT

OPERATING WEIGHT

15790 lbs+ [7165] kg+

HEAVIEST SECTION WEIGHT

9480 lbs+ [4305] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG