UNIT CLOSED CIRCUIT COOLER

MODEL # eco-ATWB 20-3J12 SCALE NTS


EVAPCO, INC. Evapeo

DWG. # WB36M1206-DRC-ST REV. SERIAL # DATE\_11/17/2025


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 2. HEAVIEST SECTION IS UPPER SECTION
  3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]

## FACE C



## **FACE A**





SHIPPING WEIGHT

29460 lbs+ [13365] kg+

OPERATING WEIGHT

44480 lbs+ [20180] kg+

HEA

HEAVIEST SECTION
WEIGHT

12170 lbs+ [5525] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR