

|                               |              |                                                                                                            |                            |                   |
|-------------------------------|--------------|------------------------------------------------------------------------------------------------------------|----------------------------|-------------------|
| UNIT<br>CLOSED CIRCUIT COOLER |              | <div>EVAPCO, INC.</div>  | DWG. #<br>WB36M1212-DRC-SF | REV.<br>-         |
| MODEL #<br>eco-ATWB 20-6K12-Z | SCALE<br>NTS |                                                                                                            | SERIAL #                   | DATE<br>2/11/2026 |

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]

FACE B


PLAN VIEW

FACE C

FACE D

FACE A



|                 |                        |                  |                        |                         |                       |                          |   |           |     |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 44980 lbs+ [20405] kg+ | OPERATING WEIGHT | 63940 lbs+ [29005] kg+ | HEAVIEST SECTION WEIGHT | 19930 lbs+ [9045] kg+ | NO. OF SHIPPING SECTIONS | 4 | DRAWN BY: | SLR |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|