UNIT CLOSED CIRCUIT COOLER

MODEL # eco-ATWB 17-6M14-Z SCALE NTS


EVAPCO, INC. Evapeo

DWG. # WB3171412-DRD-SF REV. SERIAL # DATE_11/17/2025


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE
- 6. *-APPROXIMATE DÍMENSIONS DO NOT ÚSE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]





FACE D





SHIPPING WEIGHT 42900 lbs+ [19460] kg+

OPERATING WEIGHT

59440 lbs+ [26965] kg+

HEAVIEST SECTION WEIGHT

19370 lbs+ [8790] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG