JNIT	CLOSED CIRCUIT CO	OOLER	EVAPCO, INC. Evapeo			DWG. # WB3122008-DRC-SF REV	
10DEL #	eco-ATWB 12-4L20-Z	SCALE NTS	EVAPCO, .	LINC.	SERI	AL #	DATE 11/10/2025
2. HÉAVIE 3. MPT DE FPT DE BFW DI GVD DE FLG DE PE DEN 4. + UNIT ACCES FOR AG 5. * - APPI FOR PF PIPING 7. SERIES DRAIN 3. 3/4" [19 RECOM	N MOTOR LOCATION ST SECTION IS UPPER SEC ENOTES MALE PIPE THREA NOTES FEMALE PIPE THREA NOTES BEVELED FOR WE ENOTES GROOVED NOTES FLANGE IOTES PLAIN END WEIGHT DOES NOT INCLUI SCRIES (SEE SEPARATE D CCESSORIES) JP WATER PRESSURE IIN [137 kPa], 50 psi MAX [34 ROXIMATE DIMENSIONS DO RE-FABRICATION OF CONNE FLOW PIPING AND AUX. C BY OTHERS MM] DIA. MOUNTING HOLES IMENDED STEEL SUPPORT	DEAD LDING DE RAWINGS 4 kPa] D NOT USE ECTING ROSSOVER S. REFER TO DRAWING.	FACE E PLAN VIEW	- II I	FACE C	CCESS DOOR	<u>FACE D</u>
). DIMENS	SIONS LISTED AS FOLLOWS ENGLISH FT-IN METRIC [mm]	S:	7" [178]]	1'-3 1/4" [387]	FACE A		
	J e =			1 307 1			
	(4) 4" [100] BFW FLUID IN	5'-9 1/4" *	3'-3/8" * [924] * 9'-1/8" [2748]	(4) 1/2" [15] FPT VENT	[4		
	2'-6 3/4" * [781]		(4) 4" [100] BFW FLUID OUT 15'-2 3/8" [4632]				
	2" [50] MPT — MAKE-UP — MAKE-UP — 2'-1 1/4" — [643]		(SEE	LOW PIPING NOTE 7) SSOVER DRAIN PROTECT 7)			
	3 5/8" DRA	10] MPT IN 3" [80] MI 5 1/4" OVERFLO' 133] /4" 18]	PT W				
		"-2" !184] [11'-10"		2'-1/2"			
SHIPPING WEIGHT	32110 lbs+ [145	FACE B OPER. WEI	ATING 47950 lbs+ [21750] kg+	HEAVIEST SECTION WEIGHT	27600 lbs+ [12520] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: JLG