

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-4N20-Z	SCALE NTS




DWG. #	WB3122008-DRC-SF	REV.	-
SERIAL #		DATE	2/19/2026

NOTES:

- (M) - FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]




FACE B


PLAN VIEW

FACE B

FACE C



FACE D



FACE A

SHIPPING
WEIGHT

32320 lbs+ [14665] kg+

OPERATING
WEIGHT

48160 lbs+ [21850] kg+

HEAVIEST SECTION
WEIGHT

27810 lbs+ [12615] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG