INIT	CLOSED CIRCUIT COOLER	
IODEL #	οςο-ΛΤWB 12-4L36-7	SCALE NITC

EVAPCO, INC. evapco

**FACE B** 

**PLAN VIEW** 

OPERATING

WEIGHT

58180 lbs+ [26395] kg+

DWG. # WB3123608-DRC-SF REV. SERIAL # DATE\_11/10/2025

**FACE D** 

DRAWN BY: JLG

NO. OF SHIPPING SECTIONS


## NOTES:

**SHIPPING** 


WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DÍMENSIONS DO NOT ÚSE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]

## FACE C



## FACE A



86520 lbs+ [39245] kg+

HEAVIEST SECTION

WEIGHT

25170 lbs+ [11420] kg+