UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 7-3H9

EVAPCO, INC. Evapco



REV. CW4C070906-DRA-ST


SERIAL #


DWG. #


DATE<sub>12/13/2025</sub>

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







**SHIPPING** 8810 lbs+ [4000] kg+ WEIGHT

**OPERATING** WEIGHT

11340 lbs+ [5145] kg+

HEAVIEST SECTION WEIGHT

7220 lbs+ [3275] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM