JNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 24-3N14-7	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # REV. WB3241406-DRC-SF DATE 11/21/2025 SERIAL #


FACE D

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]




FACE C



FACE B PLAN VIEW

. 7" [178] (8) 4" [100] BFW -5'-9 1/4' [1759] 3'-3/8" [924] FLUID IN 8'-3 5/8' [2532] " [100] BFW FLUID OUT 1'-10 1/4" * 15'-5 7/8" [4721] [565] 6" * 7'-2 1/4' [2189] 2'-1 1/4" [643] 4'-8" [1422] (2) 2" [50] MPT MAKE-UP 1'-5" [433] 3 5/8" [92] 11'-4 3/4" [3473] (2) 3" [80] MPT -DRAIN (2) 3" [80] MPT OVERFLOW [3499] 11'-10" [3607] 24'-1 1/8' [7344] **FACE B**

FACE A



SHIPPING WEIGHT

39200 lbs+ [17785] kg+

OPERATING WEIGHT

59360 lbs+ [26930] kg+

HEAVIEST SECTION WEIGHT

16540 lbs+ [7505] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG