



UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 7-4H18-Z	SCALE NTS

EVAPCO, INC. 

DWG. #	CW4C071808-DRA-SF	REV.	-
SERIAL #		DATE	2/5/2026

NOTES:

- (M) - FAN MOTOR LOCATION
- HEAVIEST SECTION IS FAN/CASING SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



SHIPPING
WEIGHT

19330 lbs+ [8770] kg+

OPERATING
WEIGHT

25360 lbs+ [11505] kg+

HEAVIEST SECTION
WEIGHT

16310 lbs+ [7400] kg+

NO. OF SHIPPING SECTIONS
2

DRAWN BY:
TAM