

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 24-5N14-Z	SCALE NTS

EVAPCO, INC.


DWG. #	WB3241410-DRC-SF	REV.	-
SERIAL #		DATE	2/8/2026

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. SERIES FLOW PIPING AND AUX. CROSSOVER
DRAIN BY OTHERS.
8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
9. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE B


PLAN VIEW



FACE D



FACE B



FACE A

SHIPPING WEIGHT 53620 lbs+ [24325] kg+ OPERATING WEIGHT 77580 lbs+ [35190] kg+ HEAVIEST SECTION WEIGHT 23750 lbs+ [10775] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: JLG