


| | | | | | | |
|---------|-----------------------|-----------|---|----------|-------------------|----------------|
| UNIT | CLOSED CIRCUIT COOLER | |  | DWG. # | CW4C141206-DRA-ST | REV. |
| MODEL # | eco-ATWB 14-3J12 | SCALE NTS | | SERIAL # | | DATE 2/16/2026 |

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



FACE B




DWG. # CW4C141206-DBA-ST


REV.

SERIAL #

DATE 2/16/2026



PLAN VIEW



FACE A

SHIPPING WEIGHT 21820 lbs+ [9900] kg+ OPERATING WEIGHT 28800 lbs+ [13065] kg+ HEAVIEST SECTION WEIGHT 9010 lbs+ [4090] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: TAM