

UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-ATWB 14-5K14

EVAPCO, INC. 

DWG. # CW4C141410-DRB-ST

REV -


SERIAL #

DATE: 2/16/2026

NOTES


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]




FACE B

PLAN VIEW



FACE A



SHIPPING
WEIGHT

34120 lbs+ [15480] kg+

OPERATING
WEIGHT

44420 lbs+ [20150] kg+

HEAVIEST SECTION
WEIGHT

14870 lbs+ [6745] kg+

NO. OF SHIPPING SECTIONS

4

DRAWN BY: **JLG**