UNIT	CLOSED CIRCUIT COOLER			
MODEL #	eco-ATWB 7-6K28-Z	SCALE	NTS	

EVAPCO, INC. Evapco

DWG.#	CW4C072812-DRA-ST	REV	-
SERIAL#		DATE:	12/15/2025

NOTES

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE
- ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING **PIPING**
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

38660 lbs+ [17540] kg+


WEIGHT

WEIGHT

8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN METRIC [mm]

FACE C



FACE A

17140 lbs+ [7775] kg+



WEIGHT

50100 lbs+ [22725] kg+