


UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 7-3H9	SCALE NTS





DWG. #	CW4C070906-DRA-ST	REV.	-
SERIAL #		DATE	2/6/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. \*APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]



FACE B



FACE A

SHIPPING  
WEIGHT

8810 lbs+ [4000] kg+

OPERATING  
WEIGHT

11340 lbs+ [5145] kg+

HEAVIEST SECTION  
WEIGHT

7220 lbs+ [3275] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: TAM