EVAPCO, INC. evapeo N.T.S. UNIT MODEL # SERIAL # REV. EGH1214MR-DRC-ST CLOSED CIRCUIT COOLER eco-ATWB-H 12-3L14-U22 11/5/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO FPT DENOTES FEMALE PIPE THREAD NOT USE FOR PRE-FABRICATION BFW DENOTES BEVELED FOR WELDING OF CONNECTING PIPING. **GVD DENOTES GROOVED** FLG DENOTES FLANGE FACE 2 +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY **PLAN VIEW** DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 1 45 [1142] **-√** [7 178] (2) 1/2 [15] FPT VENT 56 1/4 [1427] (4) (2) 4 [100] BFW ÌNLET 5 1/2 -**CROSSOVER PIPING** 33 1/2 851] 36 3/8 ₂ 36 3/8 [922] 91 25/32 22 1/4 216 3/8 **ACCESS DOORS** (2) 4 [100] BFW OUTLET 5 7/8 [149] 2 [50] MPT 68 1/8 [1730] MĂKE-UP 25 1/4 [641] 17 [432] 3 [80] MPT 4 1/4 [108] DRAIN 3 [80] MPT 5 1/4 [133] **OVERFLOW** 86 [**2184**] FACE 1 $[\bar{3}\bar{6}0\bar{7}]$ FACE 2 OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: **SHIPPING** HEAVIEST SECTION SFR 17780 lbs+ [8065] kg+ 23990 lbs+ [10885] kg+ 34050 lbs+ [15445] kg+

WEIGHT

WEIGHT

WEIGHT