

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 7-5J12	SCALE NTS


# EVAPCO, INC.

DWG. #	CW4C071210-DRA-ST	REV.	-
SERIAL #		DATE	2/5/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -\*APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING  
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN  
METRIC [mm]



## **FACE B**



**FACE B**  
**PLAN VIEW**



## **FACE A**

SHIPPING WEIGHT 14750 lbs+ [6695] kg+ OPERATING WEIGHT 19220 lbs+ [8720] kg+ HEAVIEST SECTION WEIGHT 12850 lbs+ [5830] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: TAM