EVAPCO, INC. MODEL # N.T.S. UNIT SERIAL # EGH121802-DRB-ST CLOSED CIRCUIT COOLER eco-ATWB-H 12-1L18-U34 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY DRAWINGS) FACE 2 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** FACE 1 69 3/8 [1762] 45 [1142] - (2) 1/2 [15] FPT VENT 7 [179] 56 1/4 [1427] (2) 4 [100] BFW **ÎNLET** 6 7/8 [175] CROSSOVER -**PIPING** 28 3/8 [719] 44 3/8 [1126] 33 1/2 [851] 75 1/32 205 5/8 [1906] 5 1/2 (2) 4 [100] BFW [5223] **ACCESS** [140] OUTLET **DOORS** 5 7/8 [149] 2 [50] MPT -74 1/8 [1883] MAKE-UP 25 1/4 [641] 3 [80] MPT 17 [432] 4 1/4 [108] 3 5/8 ₋ [92] DRAIN 18'-0" [5486] 3 [80] MPT 5 1/4 [133] [483] **OVERFLOW** 86 [2184] FACE 1 FACE 2 SHIPPING OPERATING HEAVIEST SECTION NO. OF SHIPPING SECTIONS DRAWN BY: SFR 22750 lbs+ [10320] kg+ 32340 lbs+ [14670] kg+ 14140 lbs+ [6415] kg+ WEIGHT WEIGHT WEIGHT