## **EVAPCO, INC.**

N.T.S. UNIT MODEL # REV. SERIAL # EGH090902-DRB-ST CLOSED CIRCUIT COOLER eco-ATWB-H 9-1K9-U22 12/14/2025 NOTES: 6. DIMENSIONS LISTED AS FOLLOWS: 1. (M)- FAN MOTOR LOCATION **ENGLISH IN** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. \* - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY DRAWINGS) FACE 2 5. MAKE-UP WATER PRESSURE **PLAN VIEW** 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 1 48 5/8 1233 ] 35 1/8 <del>-</del> 21 3/8 [ 543 ] (2) 1/2 [15] FPT VENT 52 7/8 [ 1341 ] (2) 4 [100] BFW INLET 5 1/2 [140] **CROSSOVER PIPING** 18 1/2 [ 469 ] 33 1/2 34 1/2 [ 876 ] 3 2249/400 181 1/2 851 [1945] [4610] 5 1/2 **ACCESS** [140] (2) 4 [100] BFW **DOORS OUTLET** 2 [50] MPT 5 7/8 [ 149 ] 51 3/4 [ 1314 ] MAKE-UP 23 1/8 [ 587 ] 15 [ 381 ] 15 5/8 [ **397** ] 2 [50] MPT 4 1/4 [ 108 ] 3 [ 76 ] DRAIN 3 [80] MPT **OVERFLOW** 8'-11 1/2' 5 1/4 [ 133 ] [ 2730 ] 67 1/2 FACE 1 1714 8'-5 1/2" [ 2578 ] FACE 2 SHIPPING OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: HEAVIEST SECTION SFR 8650 lbs+ [3925] kg+ 11780 lbs+ [5345] kg+ 5040 lbs+ [2285] kg+ WEIGHT WEIGHT WEIGHT