

EVAPCO, INC. UNIT MODEL # SERIAL # N.T.S. TLEO51224-DRA-ST **COOLING TOWER** LSTE-5112 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 5'-5" [1652] 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 1 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO **PLAN VIEW** RECOMMENDED STEEL SUPPORT DRAWING
7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN (M)[METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 33" FROM CONNECTION END OF UNIT 11'-11 1/2" [3645] FACE 2 30 3/8 771] 3 [76] 10 1/2 6 [150] BFW/GVD [266] INLET 65 5/8 [1667] (2) ACCESS DOOR 10'-6 3/4" [3220]-3 [80] MPT **OVERFLOW** 1 [25] MPT MAKE-UP 2 [50] MPT 61 1/8 DRAIN 1 [1553] 26 1/4 \bigcirc (M)[667] 6 1/4 [159] 18 3/4 [476] 3 [76] 16 1/8 1 3/4 [44] 11'-11 1/2" [410] [3645] 26 1/8 FACE 2 6 [150] BFW/GVD [664] OUTLET 32 3/8 [822] [1652] FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 4130 lbs+ [1873] kg+ 6250 lbs+ [2835] kg+ 2620 lbs+ [1188] kg+ 2 WEIGHT WEIGHT WEIGHT