


UNIT	<b>COOLING TOWER</b>
MODEL #	AXS 12-19J22

DWG. #	AX122217-DRA-ST	REV.	-
SERIAL #		DATE	1/27/2026


NOTES:

- (M) FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm]



**FACE B**

**PLAN VIEW**




**FACE C**

ACCESS DOOR

**FACE D**

(2) 8" [200] ASME 150 FLG PATTERN INLET



**FACE A**