UNIT CONDENSER	EVADOO T	NG Evapco	DWG. # WV050608-DRC-ST	REV.
MODEL # LRC-101 SCALE NTS	EVAPCO, I	NC.	SERIAL #	DATE _{11/26/2025}
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH F [METRIC] [I 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	nm] FACE B [1540]	FACE C		FACE D
2'-6 3/8" * -		12'-2 [373 FACE A	7/8"	
4" [100] PE REFRIG IN	4'-3" [1297]			
4" [100] PE REFRIG OUT	2'-3" * 7'-3 1/4" [2216]			6'-7 3/4" [2026]
3 1/4" TYP	5 1/4" * 3'-1/4" [919]	ACCESS DOOR		1'-8 1/8" [511]
3" [80] MPT OVERFLOW 2" [50] MPT 1'-8 7/8" [530]	8 3/4" [222] 2 5/8" - 4 7/8" - 1'-1 5/8" [346]	[5'-6"	- 1" [25] MPT MAKE-UP	— ACCESS DOOR
5'-5/8" [1540] FACE B	[346]	[373 <u>FACE A</u>	-1]	
SHIPPING 4670 lbs+ [2120] kg+	OPERATING 6580 lbs+ [2985] kg+	HEAVIEST SECTION 4670 lbs+ [2120] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: TLS