


EVAPCO, INC.




| UNIT | MODEL # | SCALE | DWG. # | REV. | DATE | SERIAL # |
|-----------------------|----------|-------|-------------------|------|-----------|----------|
| EVAPORATIVE CONDENSER | PHC-L614 | | HCS1224S10-DRC-ST | - | 1/28/2026 | |

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTION PIPING.
- **-UNITS WITH 20HP PER FAN REQUIRE A TALLER FAN CYLINDER, ADD 5" TO THESE DIMENSIONS.
- DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm]



FACE 2
PLAN VIEW



FACE 2



FACE 1

SHIPPING
WEIGHT

25540 lbs+ [11585] kg+

OPERATING
WEIGHT

36330 lbs+ [16480] kg+

HEAVIEST SECTION
WEIGHT

16740 lbs+ [7595] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

TLS