UNIT	CONDENSER	
MODEL #	eco-ATC-264A	SCALE NTS

EVAPCO, INC. Evapco




DWG. # REV. EG091204-DRC-ST DATE 11/3/2025 SERIAL #

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN METRIC [mm]






FACE D

**FACE A** 





**SHIPPING** 9850 lbs+ [4470] kg+ WEIGHT

OPERATING WEIGHT

13770 lbs+ [6250] kg+

HEAVIEST SECTION WEIGHT

7980 lbs+ [3620] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG