EVAPCO, INC.

UNIT MODEL # SERIAL # N.T.S. TLEO51236-DRA-ST **COOLING TOWER** LSTE-5312 12/13/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 5'-5" [1652] 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 1 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN (M)[METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 33" FROM CONNECTION END OF UNIT 11'-11 1/2" [3645] FACE 2 10 1/2 3 [76] 6 [150] BFW/GVD [266] **INLET** 77 5/8 [1972] 11'-6 3/4" [3525] (2) ACCESS DOOR -3 [80] MPT **OVERFLOW** 1 [25] MPT -MAKE-UP 2 [50] MPT 61 1/8 DRAIN |[1553] 26 1/4 [667] \bigcirc (M)6 1/4 [159] 3 [76] 18 3/4 16 1/8 11'-11 1/2" [476] [410] [3645] 26 1/8 FACE 2 [664] 6 [150] BFW/GVD 32 3/8 OUTLET [822] 19 [1652] [483] FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 4400 lbs+ [1996] kg+ 6520 lbs+ [2957] kg+ 2650 lbs+ [1202] kg+ 2 WEIGHT WEIGHT WEIGHT