

EVAPCO, INC. UNIT MODEL # SERIAL # TLE040624-DRA-ST N.T.S. **COOLING TOWER** LSTE-446 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING 4'-5/8" [1234] GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 1 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO **PLAN VIEW** (M)RECOMMENDED STEEL SUPPORT DRAWING
7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 7 5/8" FROM CONNECTION END OF UNIT 5'-11 7/8" [1826] FACE 2 9 1/2 [241] 581 4 [100] MPT INLET ACCESS DOOR 60 3/4 [1543] 3 [80] MPT 8'-8 1/4" [2648] **OVERFLOW** 20 1/8 [511] 1 [25] MPT 2 [50] MPT MAKE-UP DRAIN 43 1/2 [1105] 26 1/8 [664] \bigcirc (M)11 7/8 -**-** [302] 4 3/4 [121] 15 3/4 _ 4 [100] MPT [400] 3 [76] **OUTLET** 20 7/8 [530]1 3/8 **-** [35] 15 1/8 [384] 5'-11 7/8" 4'-5/8" [1826] [1234] FACE 2 FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 1730 lbs+ [785] kg+ 2390 lbs+ [1084] kg+ 1080 lbs+ [490] kg+ 2 WEIGHT WEIGHT WEIGHT