## EVAPCO, INC.

UNIT MODEL # SERIAL # N.T.S. TLE041848-DRA-ST **COOLING TOWER** LSTE-4518 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD 4'-5/8" [ 1234 ] BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 1 **M** 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 7 5/8" 18'-0" FROM CONNECTION END OF UNIT [ 5486 ] FACE 2 10 1/2 [ 267 ] 6 [150] BFW/GVD INLET 3 76] (2) ACCESS DOORS 86 7/8 [ 2207 ] 3 [80] MPT 10'-10 3/8" [ 3312 ] **OVERFLOW** 20 1/8 [ 511 ] 1 [25] MPT -2 [50] MPT MAKE-UP DRAIN 43 1/2 [ 1105 ] 26 1/8 [ 664 ]  $\prod$  $\mathbf{H}$ (M) **M** 11 7/8 \_ [ 302 ] 6 [ 152 ] 15 3/4 6 [150] BFW/GVD 3 [ 76 ] [ 400 ] OUTLET 20 7/8 [ 530 ] 1 3/4 [ 44 ] 18'-0" 19 1/8 [ 5486 ] [ 1234 ] [ 486 ] FACE 2 FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 4960 lbs+ [2250] kg+ 6960 lbs+ [3157] kg+ 2660 lbs+ [1207] kg+ 2 WEIGHT WEIGHT WEIGHT