

EVAPCO, INC. UNIT MODEL # DATE SERIAL # N.T.S. TLETM1836-DRA-ST **COOLING TOWER** LSTE-10318L 12/8/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE 9'-9['] 3/4" **FACE 1** [2991] ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 18'-1/8" [5490] FACE 2 1 1/2 [39] 117 3/4 [2991] 52 7/8 [1343] 52 7/8 **-** [1343] **-**11 5/8 (2) 8 [200] BFW/GVD [297] INLET 77 7/8 [1979] (2) ACCESS DOOR -15'-3/8" [4583] 2 [50] MPT -102 1/2 4 [100] MPT MAKE-UP OVERFLOW [2604] 31 3/8 [797] **_** 24 <u> 1</u> [610] 7 5/8 1 7/8_ [48] 18'-1/8" [5490] [194] 3 5/8 [92] 8 [203] 17 5/8 FACE 2 [448] 31 3/4 3 [80] MPT [806] DRAIN 37 1/4 [946] 10 [250] BFW/GVD 9'-9 3/4" [2991] **OUTLET** FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 12500 lbs+ [5670] kg+ 21460 lbs+ [9734] kg+ 7680 lbs+ [3484] kg+ 2 WEIGHT WEIGHT WEIGHT