EVAPCO, INC. UNIT MODEL # SERIAL # TLE040936-DRA-ST N.T.S. **COOLING TOWER** LSTE-439L 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING 4'-5/8" [1234] GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 1 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO **PLAN VIEW** (M)RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 7 5/8" FROM CONNECTION END OF UNIT 8'-11 1/4" [2724] FACE 2 9 1/2 [241] 4 [100] MPT INLET 3 [76] 72 3/4 [1848] (2) ACCESS DOORS 9'-8 1/4" [2953] ~ 3 [80] MPT **OVERFLOW** 20 1/8 1 [25] MPT -2 [50] MPT MAKE-UP DRAIN 43 1/2 [1105] 26 1/8 [664] (M)(M)11 7/8 -6 [152] 15 3/4 _ [400] 6 [150] BFW/GVD 3 [76] OUTLET 20 7/8 [530] 1 3/4 [44] 8'-11 1/4" [2724] 15 1/8 [384] 4'-5/8" [1234] FACE 2 FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 2310 lbs+ [1048] kg+ 3330 lbs+ [1510] kg+ 1370 lbs+ [621] kg+ 2

WEIGHT

WEIGHT

WEIGHT