EVAPCO, INC. MODEL # DATE SERIAL # TLETM2436-DRA-ST N.T.S. LSTE-10224L 12/8/2025 GVD DENOTES GROOVED FOR VICTAULIC 9'-9 3/4" [2991] ACCESSORIES (SEE ACCESSORY DRAWINGS) **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 24'-1 1/8" 7344] FACE 2 1 1/2 [39] 117 3/4 [2991] 71 7/8 [1826] 71 7/8 [1826] 11 5/8 (2) 8 [200] BFW/GVD [297] INLET 77 7/8 [1979] 15'-3/8" [4583] 4 [100] MPT 102 1/2 **OVERFLOW** [2604] 24 <u> 1</u> [610] 1 7/8 [48] 24'-1 1/8" 7344] 3 5/8 [92] FACE 2

SHIPPING WEIGHT

UNIT

NOTES:

1. (M)- FAN MOTOR LOCATION

2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING

20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

4. +UNIT WEIGHT DOES NOT INCLUDE

5. MAKE-UP WATER PRESSURE

(2) ACCESS DOOR -

2 [50] MPT -

7 5/8

[194]

17 5/8

37 1/4 [946]

[448] 31 3/4

[806]

MAKE-UP

31 3/8 [797] **_**

8 [203]

COOLING TOWER

16060 lbs+ [7285] kg+

OPERATING WEIGHT

9'-9 3/4" [2991]

FACE 1

28240 lbs+ [12809] kg+

10 [250] BFW/GVD

3 [80] MPT

DRAIN

OUTLET

HEAVIEST SECTION WEIGHT

9580 lbs+ [4345] kg+

NO. OF SHIPPING SECTIONS

3