UNIT COOLING TOWER		EVADCO TRIC EVCIDEO DWG. # TV08093F-DRJ-ST	REV
MODEL # LPT-879L	SCALE NTS	EVAPCO, INC. EVEPCO SERIAL #	DATE 12/4/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELD GVD DENOTES GROOVED FLG DENOTES FLANGE 3. + UNIT WEIGHT DOES NOT INCLUD ACCESSORIES (SEE SEPARATE DRA' FOR ACCESSORIES) 4. 3/4" DIA. MOUNTING HOLES. REFE RECOMMENDED STEEL SUPPORT DRAWING 5. MAKE-UP WATER PRESSURE-20 psi 50 psi MAX 6. DIMENSIONS LISTED AS FOLLO' ENGLISH FT-IN [METRIC] MM	DING DE WINGS R TO MIN,	FACE B PLAN VIEW	FACE D
<del>-</del> 3'-11' [ 1195	'ı <del>-</del>	FACE A [6'-3" [1905]	<b>-</b> 1
4'-11 1/4" [ 1506 ]	8" [200] BFW/GVD INLET	7'-11 1/2" ACCESS — DOOR 7'-11 1/2" 2" [50] MPT —	6'-7 3/4"
31/4" TYP 8" [ 3'-1/4" [ 919 ]	200] BFW/GVD OUTLET	3" [75] MPT OVERFLOW ACCESS DOOR  2 5/8"   1'-8 1/8"   1/8 1/8"   1/41 1/2"   2" [50] MPT MAKE-UP	6'-7 3/4" [ 2026 ]
-	7'-10 1/8" [ 2391 ] <b>FACE B</b>	8 3/4"	

**FACE A**