


UNIT	COOLING TOWER
MODEL #	AXS 12-22I22

**EVAPCO, INC.**




DWG. #	AX122220-DRB-ST	REV.	-
SERIAL #		DATE	1/28/2026

NOTES:  
1. (M)- FAN MOTOR LOCATION  
2. HEAVIEST SECTION IS UPPER SECTION  
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)  
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  
6. 3/4" DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.  
7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN  
[METRIC] [mm]



**FACE B**



HEAVIEST SECTION  
WEIGHT

SHIPPING  
WEIGHT

18830 lbs+ [8545] kg+

OPERATING  
WEIGHT

39770 lbs+ [18040] kg+

10370 lbs+ [4705] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:  
JLM