




|  |  |                        |       |   |   |                        |      |                         |          |                       |  |                          |  |   |  |           |  |     |  |
|--|--|------------------------|-------|---|---|------------------------|------|-------------------------|----------|-----------------------|--|--------------------------|--|---|--|-----------|--|-----|--|
| UNIT   |  | CONDENSER              |       | <div>EVAPCO, INC.</div> <div></div> | DWG. #  | EG241404-DRC-ST        | REV. | -                       |          |                       |  |                          |  |   |  |           |  |     |  |
| MODEL #  |  | eco-ATC-816A           | SCALE |   | NTS   | SERIAL #               |      | DATE                    | 7/8/2025 |                       |  |                          |  |   |  |           |  |     |  |
| <div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div>  FPT DENOTES FEMALE PIPE THREAD</div> <div>  BFW DENOTES BEVELED FOR WELDING</div> <div>  GVD DENOTES GROOVED</div> <div>  FLG DENOTES FLANGE</div> <div>  PE DENOTES PLAIN END</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE</div> <div>  ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div>  20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. *-APPROXIMATE DIMENSIONS DO NOT USE</div> <div>  FOR PRE-FABRICATION OF CONNECTING</div> <div>  PIPING</div> <div>7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO</div> <div>  RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>8. DIMENSIONS LISTED AS FOLLOWS:</div> <div>  ENGLISH FT-IN</div> <div>  METRIC [mm]</div> |  |                        |       |   |   |                        |      |                         |          |                       |  |                          |  |   |  |           |  |     |  |
| <div><div>FACE B</div><div>PLAN VIEW</div></div> <div></div>  |  |                        |       |   | <div><div>FACE C</div><div>ACCESS DOOR</div><div>FACE D</div><div>ACCESS DOOR</div><div>FACE A</div></div> <div></div> |                        |      |                         |          |                       |  |                          |  |   |  |           |  |     |  |
| SHIPPING WEIGHT  |  | 31320 lbs+ [14210] kg+ |       | OPERATING WEIGHT  |   | 46460 lbs+ [21075] kg+ |      | HEAVIEST SECTION WEIGHT |          | 12600 lbs+ [5720] kg+ |  | NO. OF SHIPPING SECTIONS |  | 4 |  | DRAWN BY: |  | TLM |  |