


|         |               |
|---------|---------------|
| UNIT    | COOLING TOWER |
| MODEL # | AXS 14-16L24  |

NOTES:  
 1. (M)- FAN MOTOR LOCATION  
 2. HEAVIEST SECTION IS UPPER SECTION  
 3. MPT DENOTES MALE PIPE THREAD  
 FPT DENOTES FEMALE PIPE THREAD  
 BFW DENOTES BEVELED FOR WELDING  
 GVD DENOTES GROOVED  
 4. +UNIT WEIGHT DOES NOT INCLUDE  
 ACCESSORIES (SEE ACCESSORY DRAWINGS)  
 5. MAKE-UP WATER PRESSURE  
 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]  
 6. 3/4" DIA. MOUNTING HOLES. REFER TO  
 RECOMMENDED STEEL SUPPORT DRAWING.  
 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN  
 [METRIC] [mm]



**PLAN VIEW**

