

CONFIDENTIAL

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

EVAPCO, INC.



CUSTOMER

MODEL # SSTXB1-743H0050A1MA


SCALE N.T.S.

DWG. #

STXC1-SE-12

REV.

2/6/2026



Technical drawing showing dimensions for a unit. The top horizontal dimension is 67 3/8. The left vertical dimension is 6 1/4. The right vertical dimension is 19 1/8. The central horizontal dimension is 42. The bottom horizontal dimension is 42. The bottom left vertical dimension is 6 1/4. The bottom right vertical dimension is 19 1/8. A drain line is shown exiting the bottom right, labeled "1\" data-bbox="750 350 850 450" MPT DRAIN".

Technical drawing of a NEMA 4X junction box. The box is rectangular with a thickness of $1\frac{1}{4}$ inches. The top edge has a total width of $46\frac{3}{8}$ inches, with $3\frac{1}{4}$ inches on each side of a central $41\frac{3}{8}$ inch span. The bottom edge has a total width of $45\frac{3}{8}$ inches, with $1\frac{1}{8}$ inches on each side of a central $43\frac{1}{8}$ inch span. The height of the box is $37\frac{3}{8}$ inches, with a bottom cutout of 28 inches. A handle is located on the right side. An 'AIR FLOW' indicator is shown on the left side. A callout points to the left side of the box, labeled 'NEMA 4X JUNCTION BOX'.

PROJECT

ROOM

SHIPPING
WEIGHT 430 lbs

OPERATING
WEIGHT 460 lbs