UNIT	CONDENSER	
MODEL #	eco-ATC-3296A	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # REV. WB3244010-DRC-ST DATE_{12/14/2025} SERIAL #


NO. OF SHIPPING SECTIONS


NOTES:

SHIPPING

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





196560 lbs+ [89160] kg+

HEAVIEST SECTION

WEIGHT

32770 lbs+ [14865] kg+

OPERATING

WEIGHT

149220 lbs+ [67690] kg+