ATL4BI48304E5T-DRC-DS COOLING TOWER EVAPCO, INC. Evapeo SERIAL# DATE: MODEL# SCALE AT 248-5S30-EV NTS 12/4/2025 3'-4" **NOTES FACE C** [1016] 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS CASING SECTION 3. MPT DENOTES MALE PIPE THREAD 9'-10 1/8" [3000] FPT DENOTES FEMALE PIPE THREAD 14'-3 3/4" [4362] BFW DENOTES BEVELED FOR WELDING 18'-2 1/2" [5550] **GVD DENOTES GROOVED** FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) (4) 16" [400] 5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO BFW/GVD (2) ACCESS DOOR EQUALIZER RECOMMENDED STEEL SUPPORT DRAWING 6. DIMENSIONS LISTED AS FOLLOWS **FACE B FACE D ENGLISH FT-IN** 2 5/8" [67] **PLAN VIEW** [METRIC] [mm] **BOTTOM OF UNIT** 7. FOR BOTTOM INLET SPECIFICATIONS. SEE DETAIL. **TYPICAL BOTTOM INLET** BFW/GVD **CONNECTION DETAIL BOTTOM INLET** 5'-11 3/8" [1813] 7'-6" **FACE A** [2286] 7'-0" [2134] 6'-0 1/8" [1832] 31'-9 1/2" [9690] 8'-1 1/8" 7'-11 1/4" [2467] [2419] 8'-7 1/8" [2619] -2'-1 1/4" [641] 1'-5 3/8" [441] 10'-2 1/4" [3105] -3 5/8" [92] -3'-0 3/8" [923] (4) 2" [50] MPT -4 3/8" [111] 0 MAKE-UP 9'-0 7/8" [2765] 13'-4 3/8" (2) 3" [80] 10-0 7/8" L1'-11 3/4" [603] BFW/GVD (4) 3" [80] MPT FPT DRAIN [4074] [3070] ²'-9 3/8" [848] OUTLET **OVERFLOW** 11'-1 3/8" 1 3/8" 30'-2 1/4" [35] [9201] [3388] (4) 3" [80] MPT 11'-5 1/8' DRAIN [3483] 11'-6 1/8" [3508] 11'-10 3/4" [111] [3626] 24'-1 7/8" [7363] 48'-8 1/8" [14837] **FACE B FACE A** NO. OF SHIPPING SECTIONS DRAWN BY: SHIPPING OPERATING 141540 lbs+ [64205] kg+ 194600 lbs+ [88270] kg+ HEAVIEST SECTION 13200 lbs+ [5990] kg+ 14 **JLG** WEIGHT WEIGHT WEIGHT