| UNIT CLOSED CIRCUIT COOLER  | EVADOO  | TNC evapeo   | DWG. # WX41218X2412F-DRA-ST REV -        |
|---|---|--|--|
| MODEL# ESW4 12-26J18X-LF SCALE N  | EVAPCO,   | INC. evapco  | SERIAL # DATE: 10/28/202                 |
| NOTES:  1. (M)- FAN MOTOR LOCATION  2. HEAVIEST SECTION IS COIL SECTION  3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE  4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAW)  5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING  6. MAKE-UP WATER PRESSURE 20 psi MIN [137 KPa], 50 psi MAX [344 KPa]  7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]  8. * - APPROXIMATE DIMENSIONS DO NOT L FOR PRE-FABRICATION OF CONNECTING  9. COIL CONNECTIONS LOCATED ON FACES | (4) 4" [100] BFW FLUID IN SE PIPING B AND D   | FACE B PLAN VIEW  - (4) 4" [100] BFW FLUID OUT  * 3'-6" [1067] | CE C  FACE D  CE A                       |
| 2" [50] MPT MAKE-UP 3" [80] MPT DRAIN 2'-4" [711] 4" [101] 4 1/4" [107] 5 1/4" [132] 11'-10 [3607] FACE   | FACE B & D COIL CONNECTIONS  3" [80] MPT OVERFLOW  1'-7 3/8" [492] 4'-9 5/8" [1464] | (4)1/2" [15] FPT VENT 2'-1" [635]                              | 7" [178]  1'-3 1/4" [387]                |
| SHIPPING WEIGHT 35300 lbs+ [16015] kg+  | OPERATING WEIGHT 51890 lbs+ [23540] kg+   | HEAVIEST SECTION WEIGHT 28700 lbs+ [13020] kg+                 | NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT |