CLOSED CIRCUIT COOLER

ESW4 12-26N18-LF

EVAPCO, INC. EVAPCO



WX412182412F-DRA-ST

SERIAL#


11/4/2025

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]
- 8. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING




FACE C



FACE A



NTS



SHIPPING 35280 lbs+ [16005] kg+ WEIGHT

OPERATING WEIGHT

51850 lbs+ [23520] kg+

HEAVIEST SECTION WEIGHT

28200 lbs+ [12795] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

AWT