CLOSED CIRCUIT COOLER	EV/ADCO '	TNC evapeo	DWG. # WX41218X3606P-DRA-ST REV -
MODEL# ESW4 12-33N18X-SP SCALE NT	EVAPCO, .	INC. evapeo	SERIAL# DATE: 11/6/2025
NOTES:  1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWIN 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT US FOR PRE-FABRICATION OF CONNECTING F 9. COIL CONNECTIONS LOCATED ON FACES	(2) 4" [100] BFW FLUID IN FLUID IN *2'-8" [813] FACE B & D	FACE B PLAN VIEW  (2) 4" [100] BFW FLUID OUT  * 1'-7 1/2" [495]  FACE B PLAN VIEW  (2) 4" [100] BFW FLUID 3 FACE  * 4'-7" * 2'-3 3/8" [695]	T" [178]  7" [178]  7" [178]
2" [50] MPT MAKE-UP 3" [80] MPT DRAIN 2'-4" [711] 4 1/4" [107] 5 1/4" [132] 11'-10" [3607]	4'-9 5/8" [1464]	(2)1/2" [15] FPT VENT	(M)   ACCESS   DOOR   9'-3 7/8" [2843]   18'-6 5/8" [5656]   9'-2 3/4" [2813]   2'-3 1/2"   [699]   CE A
SHIPPING WEIGHT 23150 lbs+ [10505] kg+	OPERATING WEIGHT 34880 lbs+ [15825] kg+	HEAVIEST SECTION 15280 lbs+ [6935] kg+	NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT