

UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 12-32I12-LP

SCALE NTS

EVAPCO, INC.




DWG. # WX412123604P-DRA-ST

REV -
SERIAL #
DATE: 2/10/2026

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B


FACE B
PLAN VIEW

FACE C



FACE D

FACE A



FACE A

SHIPPING
WEIGHT

13800 lbs+ [6260] kg+

OPERATING
WEIGHT

21020 lbs+ [9535] kg+

HEAVIEST SECTION
WEIGHT

8340 lbs+ [3785] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT