

UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 12-35L12-LF

EVAPCO, INC.




DWG. # WX412123610F-DRA-ST

REV -
SERIAL #
DATE: 2/14/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING




FACE B

FACE B
PLAN VIEW



FACE C



FACE A

SHIPPING
WEIGHT

22040 lbs+ [10000] kg+

OPERATING
WEIGHT

32200 lbs+ [14610] kg+

HEAVIEST SECTION
WEIGHT

16410 lbs+ [7445] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY:

AWT