

CONFIDENTIAL

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

**EVAPCO, INC.**



CUSTOMER

MODEL # SSTWB5-47S83F0075F3KA




SCALE N.T.S.

DWG # STWA5-SE

REV. 0

DATE 1/22/2026

NEMA 4X  
JUNCTION  
BOX



NOTES

- 1) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 2) HANGER HOLES ARE FOR  $\frac{3}{4}$  INCH THREADED ROD.
- \* HOT GAS DEFROST ADDS  $\frac{1}{2}$  INCH TO THE HEIGHT OF A STANDARD UNIT, WATER DEFROST ADDS 6 INCHES TO THE HEIGHT OF A STANDARD UNIT AND CHANGES THE DRAIN SIZE
- \* TWO ROWS REHEAT ADDS 5.25 INCHES TO THE HEIGHT OF 6 AND 8 ROW DEEPEP STANDARD UNITS.
- \* FOUR ROWS REHEAT ADDS 5.25 INCHES TO THE HEIGHT OF 4 AND 6 ROW DEEPEP STANDARD UNITS AND 8.75 INCHES TO THE HEIGHT OF 8 ROW DEEPEP STANDARD UNITS.
- \* \* EXTENDED WIDTH DRAIN PAN ADDS 6 INCHES TO THE WIDTH OF A STANDARD UNIT.

PROJECT

ROOM

SHIPPING  
WEIGHT

2300 lbs+ [1045] kg+

OPERATING  
WEIGHT

2670 lbs+ [1215] kg+