UNIT **CONDENSER** SCALE NTS MODEL # eco-ATC-283A

EVAPCO, INC. Evapeo




DWG. # REV. WB3090908-DRC-ST DATE 11/2/2025 SERIAL #


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





**FACE A** 





DRAWN BY: SLR NO. OF SHIPPING SECTIONS **SHIPPING OPERATING** HEAVIEST SECTION 9770 lbs+ [4435] kg+ 11210 lbs+ [5085] kg+ 14230 lbs+ [6455] kg+ WEIGHT WEIGHT WEIGHT