



UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 12-45I12-SP SCALE NTS

N


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL
SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B



FACE B
PLAN VIEW



FACE A

SHIPPING WEIGHT 18710 lbs+ [8490] kg+ OPERATING WEIGHT 27510 lbs+ [12480] kg+ HEAVIEST SECTION WEIGHT 12760 lbs+ [5790] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: AWT