UNIT	CONDENSER	
MODEL #	eco-ATC-313A	SCALE NTS

EVAPCO, INC. Evapco




DWG. # REV. EG091404-DRC-ST DATE_{10/31/2025} SERIAL #


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN**

METRI C [mm]

FACE C ACCESS DOOR **FACE B FACE D PLAN VIEW**

FACE A





DRAWN BY: JLG NO. OF SHIPPING SECTIONS **SHIPPING OPERATING** HEAVIEST SECTION 11160 lbs+ [5065] kg+ 9080 lbs+ [4120] kg+ 15710 lbs+ [7130] kg+ WEIGHT WEIGHT WEIGHT