CLOSED CIRCUIT COOLER EVAPCO, INC. Evapeo WX409123608P-DRA-ST MODEL# SERIAL# ESW4 9-34K12-SP 11/5/2025 NTS NOTES: 1. (M)- FAN MOTOR LOCATION **FACE C** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD (M) FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING _ = = = **GVD DENOTES GROOVED** FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. **FACE B FACE D** REFER TO RECOMMENDED STEEL **PLAN VIEW** SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm] **FACE A** 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING ¬1'-0 7/8" [327] [(W)] * 2'-8" ACCESS (M) (DOOR [813] 8'-3 1/4" [2522] 4" [100] BFW 4" [100] BFW FLUID OUT FLUID IN 17'-1 3/8" [5218] 3" [80] MPT **OVERFLOW** 1/2" [15] FPT 2" [50] MPT MAKE-UP VENT -* 2'-3" [686] 2" [50] MPT DRAIN 8'-10 1/8" [2696] 2'-3" [686]-L* 2'-2 3/8" [670] 3 3/8" [86]-L1'-6 3/8" [465] 2'-1" 11'-11 3/4" [635] [3651] 2'-5 5/8" 4 1/4" [752] [107] * 2'-10 3/4" 5 1/4" [883] [132] 8'-5 1/2" [2578] **FACE A FACE B** NO. OF SHIPPING SECTIONS DRAWN BY: OPERATING SHIPPING 13910 lbs+ [6310] kg+ 20110 lbs+ [9125] kg+ HEAVIEST SECTION 10080 lbs+ [4570] kg+ **AWT**

WEIGHT

WEIGHT

WEIGHT