| UNIT CLOSED CIRCUIT COOLER | | | | | DWG. # WX409123612P-DRA-ST | REV _ |
|--|---------------------|---|----------------------------|------------------------|--|-----------------|
| MODEL # | NTS | EVAPCO, | TUC. | Evaseo | SERIAL# | DATE: 11/1/2025 |
| NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAW 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN | /INGS) | | FACE B PLAN VIEW | FACE C | FACE D | |
| [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT FOR PRE-FABRICATION OF CONNECTIN | | | | FACE A | _[1'-0 7/8" [327] | |
| (M) * 2'-8" [813] | | | | | (ACCESS) (DOOR) 8'-3 1/4" [2522] | |
| 4" [100] BFW — FLUID IN 2" [50] MPT — MAKE-UP | | 4" [100] BFW FLUID OUT 3" [80] MPT OVERFLOW -* 3'-6" [1067] | 1/2" [15] FPT VENT | | 18'-4 3/ | 8" [5599] |
| 2" [50] MPT DRAIN | 8 | T | | | 10'-1 1/8" [3077] | |
| 3 3/8" [86] 4 1/4" [107] | - | * 2'-2 3/8" [670] -1'-6 3/8" [465] _2'-5 5/8" | 2'-1' [635 | "11'-11 3/4" [3651] | | |
| 5 1/4" [132] <u>8'</u> -5 1 [257 FACE | 8] | _* 2'-10 3/4" [883] | | FACE A | | |
| SHIPPING WEIGHT 16890 lbs+ [7665] kg+ | OPERATING WEIGHT | 24150 lbs+ [10955] kg+ | HEAVIEST SECTION WEIGHT | 13170 lbs+ [5975] kg+ | NO. OF SHIPPING SECTIONS 2 | DRAWN BY: AWT |