

UNIT CLOSED CIRCUIT COOLER
MODEL # ESW4 9-46L12-SP SCALE NTS

EVAPCO, INC.




DWG. # WX409124812P-DRA-ST

REV -


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL
SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
8. * - APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING PIPING




[...]

FACE A



FACE B
PLAN VIEW



FACE A

**SHIPPING
WEIGHT**

17380 lbs+ [7885] kg+

**OPERATING
WEIGHT**

24640 lbs+ [11180] kg+

HEAVIEST SECTION WEIGHT

13140 lbs+ [5960] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY

AWT